



VALIANT IGS V2520

Safety Specification

EN ISO 20345:2022 S7L FO HRO LG SR SC





BOARD KENNEDY GRATING
STED SLIP-TESTED



CHEQUER PLATE



HARD-WEARING SCUFF CAP







TOECAP



FUEL OIL-RESISTANT











Description

- A lightweight waterproof safety hiker with a smooth black full grain leather upper
- Feet stay dry and cool with a breathable waterproof lining
- Toes stay protected with a fibreglass toecap
- Underfoot is safe with a flexible composite midsole
- Micro-adjustable precision fit with the BOA® Fit System

Toecap

Feet are kept safe from heavy or dropped items with a strong but lightweight fibreglass toecap, tested to 200 Joules.

Protective midsole

Feet are kept safe from sharp items entering underfoot with a strong but lightweight composite anti-penetration midsole, tested to 1,100N.

Size

Available in sizes: **6 - 13** (39 - 48) including 6.5 and 10.5

Weight

725g based on a size 8 (42)

Sole

Slip safety ensured with the innovative IGSTM sole unit, featuring ladder grips for working safely at height and a water-dispersing tread to keep the wearer stable on slippery and contaminated surfaces.

Fastening

The BOA® Fit System delivers micro-adjustable, precision fit, engineered to perform in the toughest conditions. Built for gloves and freezing temperatures.

Upper

Cool and dry feet thanks to a smooth full grain water-resistant leather upper.

Footbed

Feet remain cool and sweat-free with a heel pump and heat-reducing airflow channels, while cushioned and resilient rebound PU open-cell foam offers superb comfort and support.

Lining

Feet stay dry and cool with advanced waterproof lining, featuring inside-boot climate-control technology.

Warranty

We're so confident that our boots will stand the test of time, we offer a 200-day guarantee as standard.



The BOA* Fit System is guaranteed for the lifetime of the product on which it is integrated.

EN ISO 20345:2022 standards for general purpose safety footwear, plus additional (optional) safety features.

		_	_	_	_	_	_	_	_	_	_	_	_		
Features	Test Performed	Safety Classifications													
		SB	S1	S2	S3	S3L	S3S	S4	S5	S5L	S5S	S6	S7	S7L	S7S
	Slip resistance now seen as mandatory, so no symbol given	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark	\checkmark
SB	Safety toecap protection only, tested with 200 J impact and 15 kN compression force	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Α	Anti-static: electrical resistance between foot and ground of between 0.1 and 1,000 mega ohms*		✓	✓	✓	✓	✓	✓	✓	\checkmark	✓	✓	✓	✓	✓
Е	Energy absorption of the seat region: energy absorbed to be not less than 20 J		✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
WPA	Water penetration and absorption (water-resistant and breathable)			✓	✓	✓	✓					✓	✓	✓	✓
WR	Water-resistant footwear (waterproof membrane)											✓	✓	✓	✓
Р	(Metal insert type P) Penetration-resistant outsole: Lowest penetration value required shall not be less than 1,100 N $$				✓				✓				✓		
PL	(Non-metal insert type PL) Penetration-resistant outsole: Lowest penetration value required shall not be less than 1,100 N and no separation of the layers shall occur during all tests					✓				✓				✓	
PS	(Non-metal insert type PS) Penetration-resistant outsole: Average penetration value shall not be less than 1,100 N with no single value shall be lower than 950 N						✓				✓				✓

Additional Safety Features

HRO	Heat-resistant outsole compound: shall withstand 300°C for 60 seconds
FO	Resistance to fuel oil
LG	Ladder grip
SC	Scuff cap abrasion resistance
CR	Cut-resistant upper: cut-resistant index to exceed 2.5
M	Metatarsal protection 100 J impact energy
SR	Slip test will feature glycerine on ceramic tile surface
С	Partially conductive footwear. The electrical resistance shall not be greater than 0.1 mega ohms between foot and ground*
Cl	Insulation against the cold: 30 minutes at -17°C, the decrease shall not be more than 10°C
HI	Insulation against heat: 30 minutes at 150°C, the rise shall not be higher than 22°C
AN	Ankle protection: 10 N impact mean transferred force shall not exceed 10 kN and no single value shall exceed 15 kN

FOOT HEALTH

For foot health advice, scan the QR code.



BOOT CARE

For boot care advice, scan the QR code.



